

Computer Cable, 6-ft. Bi-Directional Parallel Printer, Cen36M to DB25M

MODEL NUMBER: P602-006



Description

Tripp Lite's 6-ft. bi-directional parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. The cable has DB25 male/Cent36 male connectors and supports bi-directional communication. It is manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Bi-directional communication allows your printer to broadcast printer error messages back to network computers. Use IEEE cable if IEEE specifications are required. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Supports bi-directional communication
- Length 6-ft. Connectors: DB25 male/Cent36 male
- Superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Use IEEE cable if IEEE specifications are required

Specifications

OVERVIEW		
UPC Code	037332013439	
CONNECTIONS		
Side A - Connector 1	DB25 (MALE)	
Side B - Connector 1	CENTRONICS 36 (MALE)	
PHYSICAL		

Highlights

- Superior molded cables with integral strain relief and foilshielding for maximum EMI/RFI protection
- Provides superior conductivity and support for high-speed bidirectional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with Bi-Directional communication (although not essential)

Package Includes

• 6-ft. Bidir Parallel Cable Cen36M to DB25M



Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 0.75	
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 1.90	
Shipping Weight (lbs.)	0.50	
Shipping Weight (kg)	0.23	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.