



# AB Parallel Printer Cable (DB25 to Cen36 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P606-006



#### **Features**

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 6-ft. Connectors: DB25 male/Cent36 male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

# **Specifications**

OVERVIEW		
UPC Code	037332013521	
Technology	Parallel	
CONNECTIONS		
Side A - Connector 1	DB25 (MALE)	
Side B - Connector 1	CENTRONICS 36 (MALE)	
PHYSICAL		
Color	Black	

## **Highlights**

- Superior molded cables with integral strain relief and foilshielding for maximum EMI/RFI protection
- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bidirectional printing.

#### **System Requirements**

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

## **Package Includes**

 6-ft. AB Parallel Printer Cable DB25M to Cen36M





Cable Jacket Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.48	
Shipping Weight (kg)	0.22	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.