



# PS/2 (3-in-1) Cable Kit for KVM Switch B007-008, 10 ft. (3.05 m)

### MODEL NUMBER: P753-010



### Description

This PS/2 (3-in-1) KVM cable kit connects a PS/2 computer to a B007-008 KVM switch. This premium 3in-1 cable is made using innovative cabling that is low profile and super flexible, while maintaining the superior performance exhibited in our other KVM cables. The 3-in-1 design features a VGA (HD15) monitor connector with two PS/2 (MiniDIN6) Keyboard/Mouse connectors all bonded into a single unit. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

### Features

- Connects a PS/2 computer to a B007-008 KVM switch
- Connects a PS/2 computer or PS/2 KVM switch to a Console Extender Kit
- KVM Switch side of the cable kit consists of a HD15 Female cable, a PS/2 (MiniDIN6) Mouse cable and a PS/2 (MiniDIN6) Keyboard cable
- Computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Keyboard cable
- · Innovative, low profile design allows the cable to be incredibly flexible and easy to control
- · Gold plated copper contacts offer superior conductivity
- Double shielding (foil and braid) for maximum EMI/RFI protection

## **Specifications**

OVERVIEW	
UPC Code	037332119384
Accessory Type	Cable Kit
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories

### **Highlights**

- Connects a PS/2 computer to a B007-008 KVM switch
- Connects a PS/2 computer or PS/2 KVM Switch to a Console Extender Kit
- Gold plated copper contacts offer superior conductivity
- Double shielding (foil and braid) for maximum EMI/RFI protection

### **System Requirements**

- A PS/2 computer.
- A PS/2 KVM switch (model # B007-008).

#### **Package Includes**

 10-ft. (3.05 m) PS/2 Super-Flex 3-IN-1 Cable Kit for the B007-008 KVM Switch





CONNECTIONS	
KVM Switch Side 1	HD15 (Female)
KVM Switch Side 2	(x2) MiniDIN6 (Male)
Computer Side 1	HD15 (Male)
Computer Side 2	(x2) MiniDIN6 (Male)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.61
Shipping Weight (kg)	0.28
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.