



PS/2 (3-in-1) Cable Kit for NetDirector KVM Switch B020-Series and KVM B022-Series, 25 ft. (7.62 m)

MODEL NUMBER: P774-025



Description

This PS/2 (3-in-1) KVM cable kit is designed to connect a PS/2 computer to NetDirector® KVM switches (B020- and B022-Series KVM Switches). The KVM Switch side of the cable kit consists of a HD15 Male cable. The computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Male Keyboard cable. This low profile cable is incredibly flexible making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a PS/2 computer or a console converter to NetDirector KVM switches (All B020 and B022 Series KVM Switches)
- 25-ft. (7.62 m) 3-in-1 cable consists of two PS/2 keyboard/mouse cables and a monitor cable bonded into a single unit
- Provides superior performance and cable management
- Molded ends with easy-grip textured overmold
- Low profile cable is super flexible and easy to control
- · Low profile cable is super flexible and easy to control

Specifications

OVERVIEW	
UPC Code	037332121554
Accessory Type	Cable Kit
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories

Highlights

- Connects a PS/2 Computer to NetDirector KVM Switches (B020- and B022-Series KVM Switches)
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Male Keyboard cable
- Molded, color-coded connectors

System Requirements

- A PS/2 computer or an adapter (model # B015-000) for a non-PS/2 computer.
- A B020 or B022 Series KVM Switch.

Package Includes

 25 ft. (7.6 m) PS/2 Cable Kit for NetDirector KVM Switches (B020- and B022-Series KVM Switches)





PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	25	
Cable Length (m)	7.62	
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50	
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27	
Shipping Weight (lbs.)	1.21	
Shipping Weight (kg)	0.55	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.