

Serial ATA (SATA) Latching Signal Cable (7Pin/7Pin), 19-in. (48.26 cm)

MODEL NUMBER: P940-19I



Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices
- Metal latches ensure secure connections
- Support data transfer rates of up to 6.0 Gbps
- Narrow cables design simplifies cable routing and installation and improves air flow within CPU (no more big ribbons blocking air movement)
- Meets Serial ATA 1.0 standards, including Errata 029
- Cable is shielded to protect against EMI/RFI

Specifications

| OVERVIEW | |
|----------------------|-------------------|
| UPC Code | 037332118134 |
| Technology | SATA/eSATA |
| CONNECTIONS | |
| Side A - Connector 1 | 7 PIN SATA (MALE) |
| Side B - Connector 1 | 7 PIN SATA (MALE) |
| PHYSICAL | |
| Color | Red |
| Cable Jacket Color | Red |

Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI

Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

System Requirements

- Serial ATA device
- Serial ATA controller

Package Includes

- 19-in. Serial ATA (SATA) Latching Signal Cable 7Pin/7Pin, Straight/Straight



Powering Business Worldwide



| | |
|--------------------------------------|---------------------------|
| Cable Outer Diameter (OD) | 2.4/8.0mm |
| Wire Gauge (AWG) | 26 |
| Cable Length (ft.) | 1.6 |
| Cable Length (m) | 0.49 |
| Cable Length (in.) | 18 |
| Cable Length (cm) | 45.72 |
| Shipping Dimensions (hwd / in.) | 5.30 x 3.90 x 0.50 |
| Shipping Dimensions (hwd / cm) | 13.46 x 9.91 x 1.27 |
| Shipping Weight (lbs.) | 0.14 |
| Shipping Weight (kg) | 0.06 |
| Unit Dimensions (hwd / in.) | 5.300 x 3.900 x 0.500 |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.