



# eSATA, SATA-II External Signal Shielded Cable (7Pin/7Pin), 2M (6.56 ft.)

### MODEL NUMBER: P950-02M



### Features

- Connect your high-speed eSATA device to an eSATA controller
- Support data transfer rates of up to 6Gbps
- 2 Meter ( 6ft ) Cable is double-shielded to protect against EMI/RFI
- RoHS Compliant

## **Specifications**

| OVERVIEW                        |                     |
|---------------------------------|---------------------|
| UPC Code                        | 037332153869        |
| Technology                      | SATA/eSATA          |
| CONNECTIONS                     |                     |
| Side A - Connector 1            | 7 PIN ESATA (MALE)  |
| Side B - Connector 1            | 7 PIN ESATA (MALE)  |
| PHYSICAL                        |                     |
| Color                           | Black               |
| Cable Jacket Color              | Black               |
| Cable Length (ft.)              | 6.6                 |
| Cable Length (m)                | 2.01                |
| Shipping Dimensions (hwd / in.) | 5.30 x 3.90 x 0.50  |
| Shipping Dimensions (hwd / cm)  | 13.46 x 9.91 x 1.27 |

### **Highlights**

- Connect your high-speed eSATA device to a eSATA controller
- Support data transfer rates of up to 6Gbps
- Cable is double-shielded to protect against EMI/RFI

### **System Requirements**

- eSATA Device
- eSATA Controller

#### **Package Includes**

 2 Meter (6ft) eSATA (SATA-II) External Signal Cable (7Pin/7Pin)





| 0.14                      |  |
|---------------------------|--|
| 0.06                      |  |
|                           |  |
| FEATURES & SPECIFICATIONS |  |
| No                        |  |
| No                        |  |
|                           |  |
| STANDARDS & COMPLIANCE    |  |
| RoHS; EIA/ECA-310-E       |  |
|                           |  |
| WARRANTY & SUPPORT        |  |
| Lifetime limited warranty |  |
|                           |  |

1000 Eaton Boulevard Cleveland, OH 44122

United States

https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.