



SATA to eSATA Transition Cable (7Pin/7Pin), 2 ft. (0.61 m)

MODEL NUMBER: P952-002



Features

- Connect external eSATA drives to your SATA internal controller card
- SATA-II rated 6Gbps, 24", 26AWG cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)

Specifications

OVERVIEW		
UPC Code	037332145932	
Technology	SATA/eSATA	
CONNECTIONS		
Side A - Connector 1	7 PIN SATA (MALE)	
Side B - Connector 1	7 PIN ESATA (MALE)	
PHYSICAL		
Color	Red	
Cable Jacket Color	Red	
Cable Length (ft.)	2	
Cable Length (m)	0.61	
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50	
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.13	

Highlights

- Connect external eSATA drives to your SATA internal controller card
- 2ft SATA-II rated 6Gbps cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)





·		
Shipping Weight (lbs.)	0.13	
Shipping Weight (kg)	0.06	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
ENVIRONMENTAL		
Storage Temperature Range	-4° to 149°F (-20° to 65°C)	
Operating Temperature	0 ~ 40C (32F ~ 104F)	
Operating Humidity Range	10 to 90%	
Storage Humidity Range	20 to 80%	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.