



# 11.5kW 3-Phase Local Metered PDU, 208-240V Outlets (36 C13 & 9 C19), L22-20P 360-415V Input, 6 ft. (1.83 m) Cord, 0U Vertical, TAA

### MODEL NUMBER: PDU3XMV6L2220











#### **Features**

- 11.5 kW Local Metered Power Distribution Unit (PDU)
- 360-415V input with NEMA L22-20P 3-phase input connection
- 208-240V output with 36 C13 & 9 C19 single phase output receptacles
- 0U / 1778mm vertical rackmount installation supported
- Outlets are arranged in 3 local metered 15 outlet load banks
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

#### **Highlights**

- Local metered 11.5kW 3-Phase 360-415V input / 208-240V output PDU
- Set of 3 digital meters report output load level per phase in amps
- 70in / 1778mm 0U vertical format, toolless button-mount installation
- NEMA L22-20P 3 phase input; 6ft 1.8m line cord
- 36 C13 & 9 C19 single phase outlets; Included cord retention brackets
- TAA Compliant

#### **Package Includes**

- Local Metered rackmount PDU with pre-installed mounting buttons
- · Cord retention brackets
- Spare installation buttons (2 9mm / 4 6mm)
- · Rack mounting brackets
- Owner's manual

## **Specifications**

| OVERVIEW                       |                                  |  |
|--------------------------------|----------------------------------|--|
| UPC Code                       | 037332171955                     |  |
| PDU Type                       | Local Metered                    |  |
| INPUT                          |                                  |  |
| Input Phase                    | 3-Phase                          |  |
| PDU Input Voltage              | 360-415V                         |  |
| Recommended Electrical Service | Three-phase 20A 360-415V service |  |
| Maximum Input Amps             | 16                               |  |





| Maximum Input Amps Details                                   | Agency de-rated to 16A continuous   |
|--|---|
| PDU Plug Type  | NEMA L22-20P  |
| Input Cord Length (ft.)                                      | 6   |
| Input Cord Length (m)  | 1.83  |
| OUTPUT   |   |
| Output Capacity Details                                      | 11.5kW (415/240V), 11kW (400/230V), 10.6kW (380/220V), 10kW (360/208V) total capacity; 16A max per output phase (L1-L2, L2-L3, L3-L1); 16A max per C19 outlet; 12A max per C13 outlet   |
| Frequency Compatibility                                      | 50 / 60 Hz  |
| Output Receptacles   | (36) C13; (9) C19   |
| Output Nominal Voltage                                       | 208-240V  |
| USER INTERFACE, ALERTS & COM                                 | NTROLS  |
| Reported Load Segments                                       | Supports local monitoring of current for each output phase (16A balanced max per output load banks L1, L2 & L3); Outlets are color-coded and labeled for easy phase and load bank identification; L1-N feeds black outlets; L2-N feeds dark-gray outlets; L3-N feeds light-gray outlets |
| Front Panel LCD Display                                      | Set of 3 digital meters report per-phase output current in amps (L1, L2, L3)  |
| SURGE / NOISE SUPPRESSION                                    |   |
| Automatic Shut-Off   | No  |
| PHYSICAL   |   |
| Material of Construction                                     | Metal   |
| Form Factors Supported                                       | Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-<br>mount compatible racks  |
| PDU Form Factor  | Vertical (0U)   |
| Shipping Dimensions (hwd / in.)                              | 5.10 x 6.70 x 76.00   |
| Shipping Dimensions (hwd / cm)                               | 12.95 x 17.02 x 193.04  |
| Shipping Weight (lbs.)                                       | 11.50   |
| Shipping Weight (kg)   | 5.22  |
| Unit Dimensions (hwd / in.)                                  | 70.000 x 2.200 x 1.930  |
| Unit Dimensions (hwd / cm)                                   | 177.8 x 5.6 x 4.9   |
|  | 171.0 X 0.0 X 4.0   |
| Unit Weight (lbs.)   | 8.00  |
| Unit Weight (lbs.) Unit Weight (kg)                          |   |
|  | 8.00  |
| Unit Weight (kg)   | 8.00  |
| Unit Weight (kg)  ENVIRONMENTAL                              | 8.00<br>3.63  |
| Unit Weight (kg)  ENVIRONMENTAL  Operating Temperature Range | 8.00<br>3.63<br>0C ~ 40C (32F ~ 104F)   |





| WARRANTY & SUPPORT                     |                         |
|--|-------------------------|
| Product Warranty Period<br>(Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.