




1.9kW Single-Phase Local Metered PDU, 120V Outlets (28 5-15/20R), L5-20P/5-20P Adapter, 15 ft. (4.57 m) Cord, 0U Vertical

MODEL NUMBER: PDUMV20











Highlights

- Local Metered single phase 120V 16A 0U 60in / 152cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA L5-20P plug and 5-20P adapter
- 28 NEMA 5-15/20R outlets
- Toolless button mount and boltdown bracket installation hardware included

Package Includes

- PDUMV20 Local Metered Vertical PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

Features

- 20A single phase 120V Local Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA L5-20P input plug with 15-ft. (4.57 m) line cord and 5-20P adapter
- 0U 60in / 152cm vertical rackmount format installs using no rack spaces
- 28 NEMA 5-15/20R outlets
- Includes 20A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW		
UPC Code	037332132543	
PDU Type	Local Metered	
INPUT		
Input Phase	Single-Phase	
PDU Input Voltage	120	
Recommended Electrical Service	Single-phase 20A 120V service	
Maximum Input Amps	16	
Maximum Input Amps Details	Agency de-rated to 16A continuous	





PDU Plug Type	NEMA 5-20P; NEMA L5-20P	
Input Cord Length (ft.)	15	
Input Cord Length (m)	4.57	
OUTPUT		
Output Capacity Details	1.92kW (120V) / 16A total capacity; 16A max per outlet	
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(28) 5-15/20R	
Output Nominal Voltage	120V	
Overload Protection	20A circuit breaker	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Digital meter reports PDU output current in amps	
Switches	Lighted on/off switch with integrated transparent saftey cover	
SURGE / NOISE SUPPRESSION		
Automatic Shut-Off	No	
PHYSICAL		
Material of Construction	Aluminum	
Form Factors Supported	Vertical	
PDU Form Factor	Vertical (0U)	
Shipping Dimensions (hwd / in.)	2.40 x 3.50 x 63.20	
Shipping Dimensions (hwd / cm)	6.10 x 8.89 x 160.53	
Shipping Weight (lbs.)	7.00	
Shipping Weight (kg)	3.18	
Unit Dimensions (hwd / in.)	60.470 x 1.500 x 1.640	
Unit Dimensions (hwd / cm)	153.59 x 3.81 x 4.17	
Unit Weight (lbs.)	5.39	
Unit Weight (kg)	2.44	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-22° to 122°F (-30° to 50°C)	
Relative Humidity	5% to 95% non-condensing	
Operating Elevation	0-10000 ft. (0-3000 m)	
STANDARDS & COMPLIANCE		





Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1	
Product Compliance	RoHS; Trade Agreements Act (TAA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.