



**Tripp Lite**  
 1111 West 35th Street  
 Chicago, IL 60609 USA  
 Telephone: +(773) 869 1234  
 E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PK3022ET

### Notebook Peripheral Kit (Network Cable, Mouse and Hub) - Notebook/Laptop Computer Peripheral Devices

#### Highlights



- Micro fiber pouch (80% polyester and 20% nylon) provides easier portability while traveling and can be used as a non-scratch notebook screen wipe
- Mini optical USB mouse with 27" retractable cord works on virtually any surface and includes a quiet scrolling wheel; 480 dpi resolution and 450 mm/s tracking speed
- USB 2.0 4-port hub allows you to connect up to four USB peripherals to your notebook and supports high-speed data transfer rates
- Retractable RJ45 network cable (51" or 1.3 M long fully extended) plugs into any RJ45 jack for easy connection to the Internet or a network

#### Description

A two-in-one micro fiber pouch sets this kit apart from all the others. It acts as a convenient carrier for an included hub, mouse and RJ45 cable, and can also be used as a non-scratch screen wipe.

#### Applications

- Notebook computers

#### System Requirements

- Network Cable: USB port
- Mouse: Windows 98SE/ME/2000/XP/NT and USB port
- Hub: Windows 98SE/ME/2000/XP or Mac OS X or higher and USB port

#### Specifications

<b>OVERVIEW</b>	
Model Type	Peripheral Kits
<b>PRODUCT OVERVIEW</b>	
Product Overview	Notebook Peripheral Kit (Network Cable, Mouse, Hub)
<b>PHYSICAL</b>	
Unit weight (lbs)	0.26
Unit Dimensions (in)	7.5 x 3.7 x 1 (L x W x H)
Color	black case with silver components
<b>CONNECTIONS</b>	
Ports	4-port hub
<b>SPECIAL FEATURES</b>	
Mouse Tracking Speed	450 mm/s

<b>Resolution</b>	Mouse: 480 dpi
<b>USB 1.1 Compatible</b>	Yes
<b>USB 2.0 Compatible</b>	Yes
<b>USB Powered</b>	Yes
<b>CERTIFICATIONS</b>	
<b>Certifications</b>	FCC and CE
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	1-Year Limited Warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3177](http://www.tripplite.com/en/products/model.cfm?txtModelID=3177).