



12-Outlet Vertical Power Strip, 120V, 20A, Hardwired Input, 36 in.

MODEL NUMBER: PS3612-20HW









Highlights

- AC input hardwired via knockout on unit
- 12 outlets
- 20-amp capacity
- Ideal for applications requiring permanent installation

Package Includes

- PS3612-20HW
- · Instruction manual

Description

PS3612-20HW Power Strip offers 20A multi-outlet AC power distribution in a convenient 36-inch hardwire cabinet. Includes knockout panels to accept 3/4-inch conduit fittings for hardwire installation and 12 output receptacles with three-inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

Features

- Versatile all-metal 36 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 12 outlets total: 2 NEMA 5-15/20R (20A) and 10 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW		
UPC Code	037332042385	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	20A 120V	
Voltage Compatibility (VAC)	120	
Input Plug Type	Hard-wire	
Input Cord Length (ft.)	0	





Right-Angle Plug	No	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(2) 5-15/20R; (10) 5-15R	
Circuit Breaker (amps)	20	
Transformer Accommodation	(6) Yes	
Right-Angle Outlets	No	
Outlet Spacing	2.99 in.	
PHYSICAL		
Color	Beige	
Material of Construction	Metal	
Housing Color	Beige	
Mounting Holes or Slots	No	
Outlets Measurement (Center to Center)	4 in.	
Receptacle Color	Beige	
Shipping Dimensions (hwd / in.)	2.50 x 2.60 x 41.00	
Shipping Dimensions (hwd / cm)	6.35 x 6.60 x 104.14	
Shipping Weight (lbs.)	3.65	
Shipping Weight (kg)	1.66	
Unit Dimensions (hwd / in.)	1.500 x 1.500 x 36.000	
Unit Dimensions (hwd / cm)	91.44 x 3.8 x 3.8	
Outlet Spacing	2.99 in.	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.