



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS-415-HGULTRA

Power Strip - Agency-Approved for Use in Patient-Care Areas



Highlights

- Fully tested, certified and compliant with UL 60601-1 and UL 60950-1
- 4 hospital-grade outlets with safety covers
- Switchless design prevents accidental shutoff
- 15-ft. cord with hospital-grade plug
- Rugged all-metal case
- Approved for use within 6-ft. of patient-care areas

Description

Offering 15A AC power distribution for 120V applications in a rugged all-metal case, Tripp Lite's PS-415-HGULTRA is agency approved for use in a variety of healthcare venues, including physicians' offices, imaging centers, laboratories and more. Featuring unique, patented (U.S. No. 7,375,939), it resets automatically with no need for action by the user. Features include switchless design to prevent accidental shutoff, four NEMA 5-15R-HG hospital-grade outlets with safety covers, NEMA 5-15P-HG hospital-grade plug, 15A resettable circuit breaker, and optional-use keyhole mounting slots and flanges.

Applications

- AC power distribution with hospital-grade receptacles and plug in healthcare applications where durability and reliability are required, including areas where NEC requires hospital-grade receptacles

Package Includes

- PS-415-HGULTRA Medical-Grade Power Strip
- Owner's manual with warranty information

Features

- Rugged all-metal housing stands up to the most demanding environments
- 4 x NEMA 5-15R-HG outlets with safety covers
- 15-ft. cord with NEMA 5-15P-HG plug
- Switchless design prevents accidental shutoff
- 15A circuit breaker
- Multiple installation options with integral mounting flanges and slots
- UL60601-1 and UL 60950-1 compliant
- U.S. Patent No. 7,375,939

Specifications

OVERVIEW

Model Type	NOT For Use in Patient Areas
SYSTEM OVERVIEW	
Voltage compatibility	120VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output volt amp capacity (amps)	15A
Overload protection	15A resettable circuit breaker
Outlet quantity / type	4 x NEMA 5-15R-HG Hospital-Grade
Outlet safety covers	Yes
Outlet orientation	Single row of 4
INPUT	
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P-HG Hospital-Grade
Input cord length (ft.)	15
Input cord length (m)	4.572
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Unit Dimensions (HWD/in)	1.5 x 13.75 x 2.5
Unit Dimensions (HWD/cm)	3.8 x 34.9 x 6.4
Unit weight (lbs)	3.2
Unit weight (kg)	1.5
Material of construction	Metal
Integrated keyhole mounting tabs	Yes
Receptacle Color	White
AC line cord color	White
SPECIAL FEATURES	
Appearance	Attractive all-white color scheme
CERTIFICATIONS	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3341.

© 2010 Tripp Lite. All Rights Reserved.