



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PS-415-HGULTRA

### Medical-Grade Power Strip for Use in Patient-Care Areas with 4 Outlets and Safety Covers



#### Highlights

- Fully tested, certified and compliant with UL 60601-1 and UL 60950-1
- 4 hospital-grade outlets with safety covers
- Switchless design prevents accidental shutoff
- 15-ft. cord with hospital-grade plug
- Rugged all-metal case
- Approved for use within 6-ft. of patient-care areas

#### Description

Offering 15A AC power distribution for 120V applications in a rugged all-metal case, Tripp Lite's PS-415-HGULTRA is agency approved for use in a variety of healthcare venues, including physicians' offices, imaging centers, laboratories and more. Featuring unique, patented (U.S. No. 7,375,939), it resets automatically with no need for action by the user. Features include switchless design to prevent accidental shutoff, four NEMA 5-15R-HG hospital-grade outlets with safety covers, NEMA 5-15P-HG hospital-grade plug, 15A resettable circuit breaker, and optional-use keyhole mounting slots and flanges.

#### Applications

- AC power distribution with hospital-grade receptacles and plug in healthcare applications where durability and reliability are required, including areas where NEC requires hospital-grade receptacles
- Patient rooms, treatment rooms, exam rooms, etc.

#### Package Includes

- PS-415-HGULTRA Medical-Grade Power Strip
- Owner's manual with warranty information

#### Features

- Approved for use in Patient Care Areas
- Rugged all-metal housing stands up to the most demanding environments
- 4 x NEMA 5-15R-HG outlets with safety covers
- 15-ft. cord with NEMA 5-15P-HG plug
- Switchless design prevents accidental shutoff
- 15A circuit breaker
- Multiple installation options with integral mounting flanges and slots
- UL60601-1 and UL 60950-1 compliant

## Specifications

<b>OVERVIEW</b>	
Model Type	For Patient-Care Areas
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload protection	15A resettable circuit breaker
Outlet quantity / type	4 NEMA 5-15R-HG
Outlet safety covers	Yes
Outlet orientation	Single row of 4
<b>INPUT</b>	
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P-HG
Input cord length (ft.)	15
Input cord length (m)	4.572
Voltage compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Unit Dimensions (HWD/in)	1.5 x 13.75 x 2.5
Unit Dimensions (HWD/cm)	3.8 x 34.9 x 6.4
Unit weight (lbs)	3.2
Unit weight (kg)	1.5
Material of construction	Metal
Integrated keyhole mounting tabs	Yes
Receptacle Color	White
AC line cord color	White
Outlets center to center measurement	92mm
Keyhole slot center to center measurement	261.92mm
<b>SPECIAL FEATURES</b>	
Appearance	Attractive all-white color scheme
<b>CERTIFICATIONS</b>	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)

**WARRANTY****Product Warranty Period  
(U.S., Canada & Puerto  
Rico)**

Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3341](http://www.tripplite.com/en/products/model.cfm?txtModelID=3341).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.