



16-Outlet Vertical Power Strip, 15 ft. (4.57 m) Cord, 5-15P, 48 in.

MODEL NUMBER: PS4816











Highlights

- 16 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15-ft. cord
- 48" length

Package Includes

- PS4816
- Mounting hardware
- Instruction manual

Features

- Sturdy all-metal 48 inch corded strip format with 2.717 inch center-to-center outlet spacing
- Includes 16 NEMA 5-15R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- · Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW		
OVERVIEW		
UPC Code	037332011466	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	15	
Right-Angle Plug	No	
Input Cord Length (m)	4.57	





Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(16) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(8) Yes	
Right-Angle Outlets	No No	
	2.717 in.	
Outlet Spacing	2.717 III.	
USER INTERFACE, ALERTS & CO	NTROLS	
Switches	Lighted 2 position switch controls power to all outlets	
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off	
PHYSICAL		
Color	Silver	
Material of Construction	Aluminum	
Power Cord Color	Black	
Form Factors Supported	Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications	
Housing Color	Silver	
Included Mounting Accessories	Includes mounting clips	
Mounting Holes or Slots	No	
Outlets Measurement (Center to Center)	2.71 in.	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	2.40 x 3.40 x 51.20	
Shipping Dimensions (hwd / cm)	6.10 x 8.64 x 130.05	
Shipping Weight (lbs.)	4.50	
Shipping Weight (kg)	2.04	
Unit Dimensions (hwd / in.)	1.250 x 1.500 x 48.150	
Unit Dimensions (hwd / cm)	122 x 3.8 x 3.8	
Unit Weight (lbs.)	4.3	
Unit Weight (kg)	1.95	
Outlet Spacing	2.717 in.	
FEATURES & SPECIFICATIONS		
Antimicrobial	No	
Built-In Circuit Breaker	Yes	





STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.