



# Power It! 6-Outlet Power Strip, 15 ft. (4.57 m) Cord

**MODEL NUMBER: PS615** 





### **Highlights**

- 6 outlets
- · Illuminated on/off switch
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Keyhole mounting slots

#### **Package Includes**

- PS615 power strip
- · Warranty information
- Instruction manual

#### **Description**

The Power It!® PS615 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes six NEMA 5-15R outlets, 15-foot (4.6-meter) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

#### **Features**

- 6 outlets
- 15-ft. (4.57 m) cord
- 15 amp resettable circuit breaker
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- · Keyhole support for wall mounting
- Lighted power switch
- 120V AC, 50/60Hz electrical compatibility
- UL certification

## **Specifications**

OVERVIEW		
UPC Code	037332175557	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Input Cord Gauge Type	14 gauge; SJT	





Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	15	
Right-Angle Plug	No	
Input Cord Length (m)	4.57	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	15A circuit breaker	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row of 6	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CON		
Switches	Lighted 2 position switch controls power to all outlets	
PHYSICAL		
Color	Light Gray	
Material of Construction	Plastic	
Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 101mm, distance between slot height = 28mm	
Outlets Measurement (Center to Center)	1.12 in.	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	13.10 x 2.00 x 6.00	
Shipping Dimensions (hwd / cm)	33.27 x 5.08 x 15.24	
Shipping Weight (lbs.)	2.00	
Shipping Weight (kg)	0.91	
Unit Dimensions (hwd / in.)	10.800 x 1.850 x 1.230	
Unit Dimensions (hwd / cm)	27.43 x 4.70 x 3.12	
Unit Dimensions (hwd / cm) Unit Weight (lbs.)	27.43 x 4.70 x 3.12 1.6	
·		





FEATURES & SPECIFICATIONS		
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.