

Important Note

Standards that govern use of this product vary by country and sometimes municipality. In the United States, this product is not for use in the Patient Care Vicinity, as defined in the National Electric Code (NEC). This product is approved to CSA C22.2/CuL standards and approved for use in Canada. For application guidance and product selection in your country, please consult a [Healthcare Product Specialist](#) or your own expert.

Safe-IT UL 1363 Medical-Grade Power Strip, 6x Hospital-Grade Outlets, Antimicrobial, 15 ft. (4.57 m) Cord

MODEL NUMBER: PS-615-HG



Delivers power to devices outside of patient care vicinities, including therapy rooms and administrative areas.

Features

6-Outlet Power Strip Supplies Power Outside Patient Care VicinitiesThis medical-grade power strip is for administrative areas or resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. This includes operating rooms, therapy rooms, imaging environments and administrative areas. With six NEMA 5-15R-HG outlets and a 15-foot (4.6-meter) power cord with NEMA 5-15P-HG plug, this 120V power strip complies with UL 1363.

Exclusive Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs)The PS-615-HG is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Premium Safety Features Help Ensure Proper Power ConnectionsWith no central power switch, the PS-615-HG presents no danger of accidental shutoff and cutting off power to essential devices. One resettable 15-amp circuit breaker shuts down all input if the connected load draws too much power.

Ready for Installation Straight from the BoxBuilt-in mounting flanges and integrated keyhole slots let you install the durable metal housing on any wall or other flat surface for distributing immediate power to equipment outside a patient care vicinity.

Specifications

Highlights

- UL 1363 power strip for use outside patient care vicinities
- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- NEMA 5-15P-HG plug permits connection in confined or hard-to-reach spaces
- 15 ft. (4.6 m) power cord allows flexibility in placing power strip in relationship to AC outlet
- Switchless design helps prevent accidental shutdown of essential equipment

Applications

Supply safe medical-grade power to lab, imaging and other electric components outside a patient care area

Package Includes

- PS-615-HG Medical-Grade Power Strip
- Owner's manual



Powering Business Worldwide



OVERVIEW	
UPC Code	037332100108
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Housing Color	White
Included Mounting Accessories	Keyhole mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	1.52 in.
Receptacle Color	White



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	2.00 x 5.80 x 14.10
Shipping Dimensions (hwd / cm)	5.08 x 14.73 x 35.81
Shipping Weight (lbs.)	3.30
Shipping Weight (kg)	1.50
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.