

Power Strip - Agency-Approved Hospital/Medical Outlet Strip

MODEL NUMBER: PS-615-HGULTRA



Highlights

- Versatile power distribution strip
- 6 hospital-grade receptacles and hospital-grade plug
- 15-ft. cord
- 15A resettable circuit breaker
- Double-fault safety protection

Package Includes

- PS-615-HGULTRA Power Strip
- User manual with warranty information

Description

Providing 15A capacity AC power distribution in a rugged all-metal outlet strip for 120V applications, Tripp Lite's PS-615-HGULTRA Power Strip is agency approved for use in physicians' offices, imaging centers, laboratories and medical facilities. Features include 6 hospital-grade receptacles with GFCI protection, 15-foot AC power cord and built-in resettable circuit breaker. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS: Incorporates NEMA 5-15P-HG hospital-grade plug and 6 NEMA 5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet strip

Features

- Rugged all-metal housing withstands years of use without breakage
- 6 x NEMA 5-15R-HG hospital-grade output receptacles (2 with GFCI protection)
- 15-ft. AC cord with integrated, molded NEMA5-15P-HG hospital-grade plug
- Optional-use keyhole mounting tabs and flanges.
- Switchless design prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120V, 50/60Hz electrical compatibility
- Tested to UL (USA) and cUL (Canada)
- Agency approved for use in medical facilities

Specifications

OVERVIEW	
UPC Code	037332123268
INPUT	



Powering Business Worldwide



Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.25 x 15.00 x 6.00
Shipping Dimensions (hwd / cm)	5.72 x 38.10 x 15.24
Shipping Weight (lbs.)	3.55
Shipping Weight (kg)	1.61
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Weight (lbs.)	2.4
Unit Weight (kg)	1.09
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No



Powering Business Worldwide



Built-In Circuit Breaker	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.