

UPS Replacement Battery Cartridge Kit (2 sets of 4) for select APC UPS

MODEL NUMBER: RBC12A



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from most major brands. See the UPS replacement battery page to confirm compatibility and quantity required.

Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models SU2200RM3U, SU3000RM3U, SU3000RMT3U, NS2200RM3U, NS3000RM3U, NS3000RMT3U, SU5000T, and SU5000RMT5U.
NOTE: SU5000T and SU5000RMT5U require (2) RBC12A

Specifications

| OVERVIEW | |
|---------------------------------|---|
| UPC Code | 037332118462 |
| BATTERY | |
| Included Battery Set | Contains (8) 12V 7AH sealed lead acid batteries |
| Typical Battery Lifespan | 3 - 5 years, depending on host UPS operating system |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 7.00 x 12.40 x 15.50 |



Powering Business Worldwide



| | |
|---|---|
| Shipping Dimensions (hwd / cm) | 17.78 x 31.50 x 39.37 |
| Shipping Weight (lbs.) | 44.00 |
| Shipping Weight (kg) | 19.96 |
| Unit Dimensions (hwd / in.) | 3.800 x 10.000 x 6.000 |
| Unit Dimensions (hwd / cm) | Consists of 2 pre-wired battery sets; Each measures 9.366 x 28.575 x 14.923 |
| Unit Weight (lbs.) | 44 |
| Unit Weight (kg) | 19.96 |
| ENVIRONMENTAL | |
| Relative Humidity | 0 - 95% non-condensing |
| Operating Elevation | 0-10000 ft. (0-3000 m) |
| Storage Elevation (ft.) | 0 - 50,000 |
| Storage Elevation (m) | 0 - 15,200 m |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.