



1U Rack-Mount Power Strip, 120V, 20A, 5-20P, 12 Outlets (6 Front-Facing, 6-Rear-Facing) 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215-20





Highlights

- Designed for standard 19-inch racks (1U high)
- 12 outlets (6 front / 6 rear)
- 15-ft. (4.57 m) cord
- 20-amp circuit breaker

Package Includes

- RS-1215-20
- · Warranty information
- Instruction manual

Description

The RS-1215-20 Power Strip offers 20A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rack-mount, wall-mount and under-counter installation. Uses only 1U when installed in any 19-inch rack, meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA 5-20R outlets (six front/six rear), 15-foot (4.6-meter) cord and lighted switch with cover prevents risk of accidental turn-off.

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 NEMA5-20R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord NEMA5-20P plug connection
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 20 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332099372
INPUT	





	T	
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	20A 120V	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-20P	
Input Cord Length (ft.)	15	
Right-Angle Plug	No	
Input Cord Length (m)	4.57	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(12) 5-15/20R	
Circuit Breaker (amps)	20	
Transformer Accommodation	(3) Yes	
Outlet Orientation	6 front facing / 6 rear facing	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Lighted 2 position switch controls power to all outlets	
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Power Cord Color	Black	
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported	
Housing Color	Black	
Included Mounting Accessories	Rackmount flanges	
Mounting Holes or Slots	No	
Outlets Measurement (Center to Center)	Distance between Front outlets = 2.03 in.; Distance between Rear outlets = 2.79 in.	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	9.20 x 2.60 x 20.30	
Shipping Dimensions (hwd / cm)	23.37 x 6.60 x 51.56	
Shipping Weight (lbs.)	6.11	
Shipping Weight (kg)	2.77	
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 4.000	
	1.750 X 19.000 X 4.000	





Unit Weight (lbs.)	4.6	
Unit Weight (kg)	2.09	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
Grounding	Back panel nut and bolt grounding lug	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.