




NOT for Patient-Care Vicinity - UL 1363 1U Rackmount Power Strip with 12 Hospital-Grade Outlets, 15 ft. (4.57 m) Cord

MODEL NUMBER: RS1215-HG





Medical-grade rackmount power strip with long 15 ft. cord provides power distribution outside of patientcare vicinities.

Features

Versatile Power Distribution Outside of Patient-Care Vicinities

- Ideal for use in rackmount, wallmount and under-counter installation in administrative areas and other areas outside of patient-care vicinities
- Unfiltered electrical pass-through makes this strip ideal for distributing alternate waveform UPS or generator power in rack enclosures and network closets
- 120V, 50/60 Hz power strip complies with UL 1363 specifications

Versatile Medical-Grade Solution

- 12 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- 6 outlets are on front of unit, 6 are on rear of unit
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Resettable 15A circuit breaker protects against dangerous overloads
- Illuminated on/off switch has locking safety cover to prevent accidental shut-off

Ready to Use Right Out of the Box

 Detachable mounting flanges are configurable for versatile mounting orientation in a rack, on a wall or under a counter

Specifications

OVERVIEW

Highlights

- Occupies 1U of space in a standard 19-in. rack
- Approved for use outside of patient-care vicinities
- Complies with UL 1363 specifications
- 15 ft. cord with NEMA 5-15P-HG hospital-grade plug
- 12 NEMA 5-15R-HG hospitalgrade outlets

Package Includes

- RS1215-HG UL 1363 Medical-Grade Rackmount Power Strip with 12 15A Hospital-Grade Outlets and 15 ft. Cord
- Owner's Manual





UPC Code	037332099365
MIDUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
	15
Input Cord Length (ft.)	
Right-Angle Plug	No A 57
Input Cord Length (m)	4.57
Integrated Cord Clip	No
ОИТРИТ	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R-HG
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	6 front / 6 rear
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CON	T
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount, wallmount and undercounter installation supported
Housing Color	Black
Included Mounting Accessories	Rackmount flanges
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between Front outlets = 3.28 in.; Distance between Rear outlets = 6.5 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	9.40 x 2.25 x 20.30
Shipping Dimensions (hwd / cm)	23.88 x 5.72 x 51.56





	T	
Shipping Weight (lbs.)	6.10	
Shipping Weight (kg)	2.77	
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 4.000	
Unit Dimensions (hwd / cm)	4.4 x 43.9 x 10.2	
Unit Weight (lbs.)	4.6	
Unit Weight (kg)	2.09	
FEATURES & SPECIFICATIONS		
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
Grounding	Back panel nut and bolt grounding lug	
Built-in Cable Management	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.