

SCSI/Fibre Channel - SCSI Ribbon Cable - 68 Inch

MODEL NUMBER: S014-681

Description

Tripp Lite's internal 68in (5.8ft) 50pin SCSI ribbon cable has 8 connectors and is used to connect 50pin internal devices. This is the internal 50-pin ribbon cable required for narrow and wide SCSI applications (sometimes called SCSI-1 or SCSI-2). Perfect for internal CD-ROM drives and hard drives. Our products are fully tested and certified to meet or exceed applicable industry standards. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- 68 inches long
- Eight 50sok(female) narrow SCSI connectors
- Internal 68in (5.8ft) 50pin SCSI ribbon cable with 8 connections used to connect up to eight 50pin internal devices
- · All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

Premium cabling

System Requirements

- Narrow SCSI controller
- Narrow SCSI device

Package Includes

• 68-in. internal SCSI ribbon cable 8Conn 50SOK

Specifications

| OVERVIEW | | |
|---------------------------------|------------------------|--|
| UPC Code | 037332013767 | |
| Drives Supported | 7 | |
| Technology | Ribbon/Internal; SCSI | |
| | | |
| CONNECTIONS | | |
| Side A - Connector 1 | 50 SOCKET IDC (FEMALE) | |
| Side B - Connector 1 | 50 SOCKET IDC (FEMALE) | |
| | | |
| PHYSICAL | | |
| Color | Gray | |
| Cable Length (ft.) | 5.8 | |
| Cable Length (m) | 1.77 | |
| Cable Length (in.) | 68 | |
| Shipping Dimensions (hwd / in.) | 11.75 x 7.00 x 1.25 | |
| Shipping Dimensions (hwd / cm) | 29.84 x 17.78 x 3.18 | |
| Shipping Weight (lbs.) | 0.52 | |
| Shipping Weight (kg) | 0.24 | |



| WARRANTY & SUPPORT | |
|--|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.