

Internal/External SCSI 160 LVD Ribbon Cable (HD68M/F) with Bracket, 21-in.

MODEL NUMBER: \$051-211



Highlights

- Convert an Internal SCSI port to External
- U160 LVD Rated

System Requirements

- Wide SCSI controller card
- Open slot on CPU for external HD68 bracket

Package Includes

 21 inch LVD SCSI ribbon Cable 68Pin internal/external LVD HD68M/F with bracket

Description

This handy SCSI internal/external ribbon cable converts an available internal channel on a wide SCSI controller card to an external SCSI port (HD68F). LVD rated for U160 and earlier applications.

Features

- External HD68F port comes with mounting bracket
- 21 inches long
- Constructed with "Branded" Twist-n-Flat ribbon
- · All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest ultra 320 to legacy SCSI-1 and every combination in between
- Internal/external cabling option

Specifications

OVERVIEW		
UPC Code	037332116888	
Drives Supported	1+	
Technology	SCSI; Ribbon/Internal	
CONNECTIONS		
Side A - Connector 1	INTERNAL HD68 (MALE)	
Side B - Connector 1	HD68 (FEMALE)	
PHYSICAL		



Color	Gray
Cable Length (in.)	21
Shipping Dimensions (hwd / in.)	9.30 x 7.00 x 0.75
Shipping Dimensions (hwd / cm)	23.62 x 17.78 x 1.90
Shipping Weight (lbs.)	0.33
Shipping Weight (kg)	0.15
WARRANTY & SUPPORT	
WARRANTI & SUFFORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.