



Powering Business Worldwide

31-inch Internal SCSI U320 3-Drive LVD Ribbon Cable with Terminator (4xHD68 M)

MODEL NUMBER: S063-31I



Highlights

- Premium cabling

System Requirements

- U320/U160 SCSI HBA (Host bus adapter card)
- Any internal SCSI drive or device requiring HD68M interface

Package Includes

- 31-in. Int U320 SCSI ribbon cable 4Conn 68Pin 3Drive with terminator

Description

Introducing Tripp Lite's internal SCSI Ultra320 3-drive LVD/SE cable with an active mode-conditioning T-type crimped on terminator. LVD/SE multi-mode termination enables backward compatibility to legacy single ended devices. The terminator will sense if the bus is running LVD or SE and terminate appropriately. This cable measures 31.5 inches in length from master to drive #3 and is UL rated with premium brand cabling. Meets the latest SCSI specification of ANSI (American National Standards Institute). For 5-Drive Connection, see S065-42I, or, for Round Version cables, see S073-31I and S075-42I.

Features

- Length (master to drive 3): 31.5 inches
- Supports transfer speeds up to 320Mbps
- Connect up to 3 drives or internal devices
- HD68 male connectors
- Cable includes active mode conditioning terminator T-type LVD/SE terminator with local chip (ART IDC type)
- SCSI U320 cables include active multi-mode terminators which compensate for fluctuations in the host adapter
- Constructed with premium brand twist and flat brand cable
- UL rated cable
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
UPC Code	0373321 16987
Drives Supported	3



Powering Business Worldwide

Technology	Ribbon/Internal; SCSI
CONNECTIONS	
Side A - Connector 1	INTERNAL HD68 (MALE)
Side B - Connector 1	INTERNAL HD68 (MALE)
PHYSICAL	
Color	Gray
Cable Length (ft.)	2.6
Cable Length (m)	0.79
Cable Length (in.)	31
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.