



Powering Business Worldwide

# 42-inch Internal SCSI U320 5-Drive LVD Ribbon Cable with Terminator (6xHD68 M)

MODEL NUMBER: **S065-42I**



### Highlights

- Premium cabling

### System Requirements

- U320/U160 SCSI HBA (host bus adapter card)
- Any internal SCSI drive or device requiring HD68M interface

### Package Includes

- 42-in. Internal U320 SCSI Ribbon Cable 6Conn 68Pin 5Drive with Terminator

### Description

Introducing Tripp Lite's internal ribbon SCSI Ultra320 5-drive LVD/SE cable with an active mode-conditioning T-type crimped on terminator. LVD/SE multi-mode termination enables backward compatibility to legacy single ended devices. The terminator will sense if the bus is running LVD or SE and terminate appropriately. This cable measures 42 inches in length from master to drive #5 and is UL rated with premium brand cabling. Meets the latest SCSI specification of ANSI (American National Standards Institute). For 3-Drive Connection, see S063-31I, or, for Round Version cables, see S073-31I and S075-42I. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Length (master to drive 5): 42 inches
- Supports transfer speeds up to 320Mbps
- Connect up to 5 drives or internal devices
- HD68 male connectors
- Cable includes active mode conditioning terminator T-type LVD/SE terminator with local chip (ART IDC type)
- SCSI U320 cables include active multi-mode terminators which compensate for fluctuations in the host adapter
- Constructed with premium brand twist and flat brand cable
- UL rated cable
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332116994



Powering Business Worldwide

Drives Supported	5
Technology	Ribbon/Internal; SCSI
<b>CONNECTIONS</b>	
Side A - Connector 1	INTERNAL HD68 (MALE)
Side B - Connector 1	HD68 (MALE)
<b>PHYSICAL</b>	
Color	Gray
Cable Length (ft.)	3.5
Cable Length (m)	1.07
Cable Length (in.)	42
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.64
Shipping Weight (kg)	0.29
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.