



Powering Business Worldwide

## SCSI/Fibre Channel - 42-in. Round Internal U320 5-Drive SCSI LVD/SE Cable 6Conn HD68M

MODEL NUMBER: **S075-42I**



### Description

Introducing Tripp Lite's round internal SCSI Ultra320 5-drive LVD/SE cable with an active mode-conditioning T-type crimped on terminator. LVD/SE multi-mode termination enables backward compatibility to legacy single ended devices. The terminator will sense if the bus is running LVD or SE and terminate appropriately. This cable measures 42 inches in length from master to drive #5. This cable, with its new round design, is very flexible and easy to fit into the computer's case. The round shape also significantly improves the air flow around the cables - which can be of great concern with flat ribbon cables. Meets the latest SCSI specification of ANSI (American National Standards Institute). For 3-Drive Connection, see S075-311, or, for Flat Version cables, see S063-311 and S065-42I. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Ideal for 1U servers where space is at a premium
- Round cable increases flexibility and air flow
- Length (master to drive 5): 42 inches
- Supports transfer speeds up to 320Mbps
- Connect up to 5 drives or internal devices
- HD68 male connectors
- Cable includes active mode conditioning terminator T-type LVD/SE terminator with local chip (ART IDC type)
- SCSI U320 cables include active multi-mode terminators which compensate for fluctuations in the host adapter
- Constructed with premium brand twist and flat brand cable
- UL rated cable
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

### Highlights

- Offers significant improvement in the airflow within devices, fit and management
- Can be used with all generations of SCSI devices
- Comes with U320 terminator
- Can support multiple drives

### System Requirements

- U320/U160 SCSI HBA (Host bus adapter card)
- Any internal SCSI drive or device requiring HD68M interface

### Package Includes

- 42 inch round internal U320 5-Drive SCSI LVD/SE cable 6Conn HD68M with active multi-mode terminator



Powering Business Worldwide

| OVERVIEW                            |                           |
|-------------------------------------|---------------------------|
| UPC Code                            | 037332119414              |
| Drives Supported                    | 5                         |
| Technology                          | Ribbon/Internal; SCSI     |
| CONNECTIONS                         |                           |
| Side A - Connector 1                | HD68 (MALE)               |
| Side B - Connector 1                | (3) HD68 (MALE)           |
| PHYSICAL                            |                           |
| Color                               | Gray                      |
| Cable Length (ft.)                  | 3.5                       |
| Cable Length (m)                    | 1.07                      |
| Cable Length (in.)                  | 42                        |
| Shipping Dimensions (hwd / in.)     | 9.00 x 6.75 x 2.00        |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.14 x 5.08      |
| Shipping Weight (lbs.)              | 1.16                      |
| Shipping Weight (kg)                | 0.53                      |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.