



Powering Business Worldwide

SCSI/Fibre Channel - SCSI External Cable - 6 ft.

MODEL NUMBER: **S354-006**

Description

Multi-platform SCSI II external peripheral cable C50M to C50M. This 6ft cable is designed to connect two SCSI II devices together. Manufactured using double shielded 25 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 25 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI.
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest ultra 320 to legacy SCSI-1 and every combination in between.
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Highlights

- Premium double-shielded cable
- 25 twisted-pair conductors

System Requirements

- Any external SCSI II device or controller card requiring Cen50 interface

Package Includes

- 6-ft. SCSI Cable Centronic 50M to Centronic 50M Double Shielded

Specifications

OVERVIEW	
UPC Code	037332014979
CONNECTIONS	
Side A - Connector 1	CENTRONICS 50 (MALE)
Side B - Connector 1	CENTRONICS 50 (MALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 1.00
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 2.54
Shipping Weight (lbs.)	0.92
Shipping Weight (kg)	0.42
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.