



Powering Business Worldwide

SCSI Double Shielded Cable (HD50 M/M), 6-ft.

MODEL NUMBER: S366-006



Highlights

- Premium double-shielded cable
- 25 twisted-pair conductors

System Requirements

- Any external SCSI II device or controller card requiring HD50 interface

Package Includes

- 6Ft SCSI Cable HD50M to HD50M Double Shielded

Description

Multi-platform SCSI II external peripheral cable HD50M/M. This 6ft cable is designed to connect two SCSI II (fast SCSI) devices together. Manufactured using double shielded 25 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

Features

- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 25 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI.
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
UPC Code	037332014078
CONNECTIONS	
Side A - Connector 1	HD50 (MALE)
Side B - Connector 1	HD50 (MALE)
PHYSICAL	
Color	Beige
Cable Length (ft.)	6
Cable Length (m)	1.83



Powering Business Worldwide

Shipping Dimensions (hwd / in.)	0.50 x 5.00 x 8.20
Shipping Dimensions (hwd / cm)	1.27 x 12.70 x 20.83
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.