

Internal SAS Cable, 4-Lane (SFF-8484 to 4 x SFF-8482), 24-in.

MODEL NUMBER: **S501-24N**



Highlights

- 24-inch Internal SAS Cable
- SFF-8484 to 4 x SFF-8482
- Host Controller to Target Drives...6Gbps
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- SAS Controller w/SFF-8484 connector
- SAS Drive with SFF-8482 connector

Package Includes

- 24-inch SFF-8484 to 4 x SFF-8482 Serial Attached SCSI (SAS) Cable

Description

Tripp Lite's S501-24N is a 24-inch, Internal Serial Attached SCSI (SAS) Cable. HBA Controller connector is SFF-8484, breaking out to four, SFF-8482 disk drive connectors, which supply data and power in one connection. Supports up to 6Gbps speeds.

Features

- 24-inch Internal SAS Cable, 4-Lane
- SFF-8484 to 4 x SFF-8482
- Host Controller to Target Drives...6Gbps
- Compatible with all manufacturers SAS HBA's and SAS Drives
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332160348
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8484
Side B - Connector 1	(4) SFF-8482
PHYSICAL	
Color	Black; Red; Yellow

Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	2.00 x 2.90 x 7.30
Shipping Dimensions (hwd / cm)	5.08 x 7.37 x 18.54
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.