

Internal SAS Cable, 4-in-1 32Pin (SFF-8484) to 4 x 7pin Cable, 20-in. (0.5M)

MODEL NUMBER: **S502-20N**



Highlights

- 32-pin SFF-8484 to 4 x 7-pin internal SAS cable
- Supports data rates of up to 6.0Gbs
- Straight backshell configuration
- 0.5 meter in length (20 inch)

System Requirements

- SAS Host Bus Adapter and Backplane with SFF-8484 mating connector

Package Includes

- 0.5-Meter (20 inch) Internal SAS 4-in-1 SFF-8484 to 4 x 7pin Cable

Description

This 32-pin SFF-8484 to 4 x 7-pin internal SAS cable (Serial Attached SCSI) cable is ideal for connecting SAS controllers to individual SAS/SATA disk drives. High-performance cable provides differential pair signaling with less than 5ps/m in pair skew, improved EMI protection and 3.0 Gbps data rate with rates up to 6.0 Gbps. Thinner, flexible cable enables more efficient routing, with improved airflow and thermal mechanics. Configuration of storage devices is simplified. SAS assemblies are RoHS compliant and feature a lifetime warranty.

Features

- SFF-8484 to 4 x 7pin SAS Cable - 0.5 meter (20inch)
- Supports data rates up to 6.0Gbs
- Thin, flexible cable for easy routing and increased airflow
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332149961
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8484
Side B - Connector 1	7 PIN SATA (MALE)
PHYSICAL	
Color	Red

Cable Jacket Color	Red
Cable Length (ft.)	1.7
Cable Length (m)	0.52
Shipping Dimensions (hwd / in.)	0.25 x 6.30 x 9.60
Shipping Dimensions (hwd / cm)	0.64 x 16.00 x 24.38
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.