

Internal SAS Cable, mini-SAS (SFF-8087) to mini-SAS (SFF-8087), 18-in. (0.5M)

MODEL NUMBER: **S506-18N**



Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

Package Includes

- 18inch Internal SAS Cable, SFF-8087 to SFF-8087

Description

Internal Mini-SAS Double-Ended Plug with Sidebands, SFF-8087 to SFF-8087, 36 Circuits, 30 AWG, 18 in. length, controller to backplane.

Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal mini SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to Backplane applications

Specifications

OVERVIEW	
UPC Code	037332143327
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8087
Side B - Connector 1	SFF-8087
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1.5



Powering Business Worldwide



Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / in.)	0.25 x 5.10 x 8.10
Shipping Dimensions (hwd / cm)	0.64 x 12.95 x 20.57
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.