



Internal SAS Cable, 4-Lane mini-SAS (SFF-8087) to 4xSatA 7pin, 3 ft. (0.91 m)

MODEL NUMBER: S508-003



Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

Package Includes

• 3 ft. Internal SAS Cable, SFF-8087 to 4 x 7pin SATA

Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal mini SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to hard drive applications

Specifications

OVERVIEW		
UPC Code	037332143341	
Technology	SAS; SATA/eSATA; Ribbon/Internal	
CONNECTIONS		
Side A - Connector 1	SFF-8087	
Side B - Connector 1	7 PIN SATA (MALE)	
PHYSICAL		
Color	Red	
Cable Jacket Color	Red	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Shipping Dimensions (hwd / in.)	0.50 x 1.00 x 7.90	





Shipping Dimensions (hwd / cm)	1.27 x 2.54 x 20.07	
Shipping Weight (lbs.)	0.20	
Shipping Weight (kg)	0.09	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.