

# External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to 4xInfiniband (SFF-8470), 2M (6.56 ft.), TAA

MODEL NUMBER: **S520-02M**



## Highlights

- Hi-Performance 2 Meter SAS External Cable
- Mini-SAS SFF-8088 (iSAS) to SFF-8470
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

## Package Includes

- 2 Meter SAS External SFF-8088 to SFF-8470 Cable

## Features

- External SAS Cable, Mini-SAS SFF-8088 (iSAS) to SFF-8470 - 2 Meter
- Made with High-Performance Infiniband Cable
- Supports data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connector and SFF-8088 connector in die cast zinc housing for durability
- RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332151957
Technology	SAS
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8470
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6.6

Cable Length (m)	2.01
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 8.50
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 21.59
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.