

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to 4xInfiniband (SFF-8470), 3M (9.84 ft.)

MODEL NUMBER: **S520-03M**



Highlights

- Hi-Performance 3 Meter SAS External Cable
- Mini-SAS SFF-8088 (iSAS) to SFF-8470

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

- 3 Meter SAS External SFF-8088 to SFF-8470 Cable

Features

- External SAS Cable, Mini-SAS SFF-8088 (iSAS) to SFF-8470 - 3 Meter
- Made with High-Performance Infiniband Cable
- Supports data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connector and SFF-8088 connector in die cast zinc housing for durability
- RoHS compliant

Specifications

OVERVIEW	
UPC Code	037332151964
Technology	SAS
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8470
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Shipping Dimensions (hwd / in.)	8.00 x 10.00 x 0.50



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	20.32 x 25.40 x 1.27
Shipping Weight (lbs.)	0.66
Shipping Weight (kg)	0.30
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.