

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to mini-SAS (SFF-8088), 2M (6.56 ft.)

MODEL NUMBER: **S524-02M**



Highlights

- High-performance 2-meter SAS external cable
- Mini-SAS SFF-8088 (iSAS) to Mini-SAS SFF-8088 (iSAS)

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

2-Meter SAS External, SFF-8088 to SFF-8088 Cable

Features

- 2-meter External SAS Cable, SFF-8088 to SFF-8088
- Made with High-Performance Infiniband Cable
- Support data rates from 3.0 up to 6.0 gigabytes per second
- SFF-8088 connectors in diecast zinc housing for durability
- RoHS compliant

Specifications

OVERVIEW	
UPC Code	037332151995
Technology	SAS
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8088
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50

Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	5.300 x 3.900 x 0.500
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.