

Protect It! Surge Protector with 4 Rotatable Outlets, Direct Plug-In, 1080 Joules, 3.4A USB Charger

MODEL NUMBER: **SK40RUSBB**



Highlights

- 4 rotatable outlets/direct plug-in
- 1080 joule rating
- 3.4 amp USB charging
- Diagnostic LED

Package Includes

- SK40RUSBB surge suppressor
- Owners Manual

Description

The SK40RUSBB surge suppressor offers reliable surge and line noise protection. Premium features include a compact, direct plug-in design and 4 rotatable outlets. The unique rotating design provides convenience and flexibility. Each outlet rotates independently to provide the perfect position to connect your equipment. The SK40RUSBB also includes 2 USB ports with 3.4 amps of total power that offers fast charging for smartphones, tablets, MP3 players and other portable devices. 1080 joules of surge protection to handle the strongest surge. Diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 4 rotatable outlets / direct plug-in
- Surge suppression rating: 1080 joules
- 3.4 amp USB Charger
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332184658
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Total Charging Watts	17
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 3.4A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes



Powering Business Worldwide



DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.83 x 4.13 x 3.35
Shipping Dimensions (hwd / cm)	14.81 x 10.49 x 8.51
Shipping Weight (lbs.)	0.73
Shipping Weight (kg)	0.33
Unit Dimensions (hwd / in.)	5.500 x 3.880 x 1.770
Unit Dimensions (hwd / cm)	13.97 x 8.59 x 4.50
Unit Weight (lbs.)	.70
Unit Weight (kg)	0.32
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	Yes
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 1449; UL 497A
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.