



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SMART1000LCD

SmartPro Digital UPS - Line interactive UPS for personal computers, workstations, home entertainment System and media centers

Highlights



- 1000VA / 1kVA line interactive tower UPS
- Maintains 120V nominal output over an input range of 89 to 132V
- Workstation / media-center optimized features supported via USB port (HID-PDC compliant), coaxial surge suppression, single line TEL / DSL surge suppression and four surge-only outlets
- Large backlit LCD input voltage display with dimmer switch rotates for upright visibility in shelf or tower placement
- Input: NEMA 5-15P (120V 15A) / Output: 8 NEMA 5-15R (120V)
- 3 year product warranty / \$250,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's SMART1000LCD Line-Interactive Digital UPS System offers voltage regulation, surge suppression and long-lasting battery support for personal computers, network workstations, home entertainment systems and media centers. Internal UPS circuits support entry-level PCs for up to 60 minutes or individual VCR/DVR component for as long as 3 hours during power failures. Prevents data loss, viewing interruptions, lost recordings and loss of component programming. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete power protection in an attractive black tower configuration. Includes 4 battery-supported outlets, plus 4 additional surge suppression-only outlets for items not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure, USB cable included. PowerAlert software available via free download from www.tripplite.com. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Built-in single-line RJ-11 phone suppression jacks protect modem, satellite receiver or other peripherals with a standard dialup/DSL phone connection. Set of 2.2 GHz coaxial jacks protect against surges entering on CATV, satellite or broadcast antenna connections. Built-in audible alarm and large LCD front panel voltage display indicates line power status, battery power status, battery low/replace status and voltage boost operation. The LCD display includes a dimmer switch and can be rotated for easy viewing in any application. 1000VA/500W power-handling ability supports entry-level PCs, home entertainment systems, network workstations, audio/video components. Offers 3 minutes battery runtime with a full load of 1000VA/500W and 9 minutes with a half load of 500VA/250W. 3-year warranty; \$250,000 [connected equipment insurance](#) (USA & Canada only).

Package Includes

- SMART1000LCD Digital UPS
- USB and phone cabling
- Manual with warranty information

Features

- LCD Display with dimmer switch indicates input voltage, battery capacity and a variety of operating conditions. Display is rotatable for easy viewing whether UPS is in vertical or horizontal position
- SMART1000LCD Digital Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support during blackouts
- Supports entry level PCs up to 60 minutes or single VCR/DVR components for up to 3 hours during blackouts

- Regulates brownouts as low as 89 volts back to usable levels without using battery power
- 4 UPS battery supported outlets, plus 4 additional surge suppression-only outlets
- USB port and cable enables unattended shutdown in the case of extended power failure
- HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X.
- PowerAlert software available via free download from www.tripplite.com
- Single-line phone suppression protects standard dialup/DSL phone connection
- 1000VA/500 watt power handling ability supports a variety of sensitive computer, home theater and other equipment
- 3 minutes full load runtime (1000VA/500 watts), 9 minutes half load runtime (500VA/250 watts)
- Cabinet adapts to tower format or rackmount shelf format. Rackmount (2U) format requires an optional shelf, available separately
- Supports battery replacement via built-in access panel
- 3-year product warranty
- \$250,000 [connected equipment insurance](#) (USA & Canada Only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output Watt Capacity (watts)	500
Nominal Output Voltage(s) Supported	115v; 120v
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	8 5-15R outlet(s)
Surge suppression only outlets	4 UPS outlets, 4 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Space saving right angled input plug
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	

Full load runtime (minutes)	3 min. (500w)
Half load runtime (minutes)	9 min. (250w)
DC system voltage	12V DC
Battery recharge rate (included batteries)	Less than 20 hours from 10% to 90%
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage correction	Input voltages between 89 and 104 are boosted by 14%
LEDS ALARMS & SWITCHES	
LED Indicators	Front panel LCD display
Front panel LCD display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing
Alarms	Audible alarm indicates power-failure, low-battery and overload status; alarm can be disabled using PowerAlert software
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; dimmer switch controls LCD brightness
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL / DSL protection (1 in / 1 out); Coax surge suppression jacks (1 set)
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	12 x 3.7 x 7.2
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	30.5 x 9.4 x 18.3
Secondary form factor	Horizontal desktop placement
Installed whole system dimensions in secondary form factor (height x width x depth / inches)	3.7 x 12 x 7.2

UPS dimensions in secondary form factor (height x width x depth / cm)	9.4 x 30.5 x 18.3
UPS / Power Module weight (lbs)	15.5
UPS / Power Module weight (kg)	7
UPS Shipping dimensions (height x width x depth / inches)	10.4 x 15.6 x 4.8
UPS Shipping dimensions (height x width x depth / cm)	26.5 x 39.5 x 12.3
Shipping weight (lbs)	15.8
Shipping weight (kg)	7.2
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	52.6
Battery mode BTU / hr. (full load)	536.8
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from www.tripplite.com
Communications cable	USB cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	4 milliseconds
Low voltage transfer to battery power (setpoint)	89
High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS

CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications); ROHS (Reduction of Hazardous Substances)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	3 years
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	-
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	-
Rack Accessories	SRSHELF2P	Fixed Shelf, 2U Cantilever mount. Required mounting hardware included	-
USB Hubs/Accessories	U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	-
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	-
Extended Warranties	WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3071.