

Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 6 ft. (1.83 m) Cord, 1050 Joules, UL 1363, Not for Patient-Care Rooms

MODEL NUMBER: SPS606HGRA



Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 6-ft. cord with molded right angle hospital-grade plug
- All metal housing

Package Includes

- SPS606HGRA Surge Suppressor
- Instruction manual with warranty information

Need to use a surge suppressor behind a desk or in a confined spot? The SPS606HGRA provides surge suppression with the convenience of a space-saving, right-angle hospital-grade plug for placing the units in confined areas and keyhole mounting tabs and flanges for easy installation.

Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 6-ft. AC cord with integrated, molded Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332167088
INPUT	



Powering Business Worldwide



Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	19500
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	LINE POWER PRESENT (green)
Locking Switch Cover	Locking switch cover
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N)
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Light Gray
Housing Color	White
Mounting Holes or Slots	Yes



Powering Business Worldwide



Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.20 x 14.90 x 6.70
Shipping Dimensions (hwd / cm)	5.59 x 37.85 x 17.02
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35
Unit Weight (lbs.)	3.20
Unit Weight (kg)	1.45
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.