



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SPS-615-HG

**450-Joule Commercial-Grade Surge Suppressor with Hospital-Grade plug and receptacles; diagnostic LEDs and a heavy-duty metal housing**



### Highlights

- 6 hospital-grade outlets
- 450 joule rating
- 15-ft. cord with molded hospital-grade plug
- All metal housing

### Description

Tripp Lite's SPS-615-HG offers 15A-capacity AC surge suppression and power distribution in a rugged all-metal outlet strip for 120V applications. Offers 6 AC outlets, 15-ft. AC power cord, built-in resettable circuit breaker and 450-joule AC surge suppression. Features safety-enhanced hospital grade plug and outlets. Switchless design prevents accidental shutoff. Optional use keyhole mounting tabs. 15A circuit breaker controls power to all outlets and protects against overloads. LED indicator verifies line power available.

PLUG/OUTLETS: NEMA 5-15PHG Hospital-Grade Plug and 6 x NEMA 5-15RHG Hospital-Grade AC Outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet surge suppression strip

SUPPRESSION: AC: 150V RMS Clamping/450 joules

#### Applications

- AC power distribution and surge suppression with hospital-grade receptacles and plug where durability and reliability are required. Not for use where NEC requires hospital-grade receptacles.

#### Package Includes

- SPS-615-HG Surge Suppressor
- Instruction manual with warranty information

### Features

- 450-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grad AC outlets
- 15-ft. AC cord with integrated, molded Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker

- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 listed

## Specifications

OVERVIEW	
Intended Application	Hospital/Medical
SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15
Outlet quantity / type	6 NEMA 5-15R-HG
Transformer accommodation	Supports 1 large transformer plug accessories without covering remaining outlets
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P-HG Hospital-Grade
Input cord length (ft.)	15 ft.
Input cord length (m)	4.6
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	LINE POWER PRESENT (green)
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	450 joules
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode surge suppression
Clamping voltage (RMS)	140V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	13.75 x 2.5 x 1.5
Unit Dimensions (HWD/cm)	34.9 x 6.4 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Includes keyhole mounting tabs and flanges

<b>Receptacle Color</b>	White
<b>AC line cord color</b>	Gray
<b>Style</b>	Strip
<b>CERTIFICATIONS</b>	
<b>UL1449 1998 Rev. (AC Suppression)</b>	UL1449 (Series Number: AGIB12015SL)
<b>UL1363 (Power Tap)</b>	UL1363 (Series Number: AGIB12015SL)
<b>cUL / CSA (Canada)</b>	cUL (Series Number: AGIB12015SL)
<b>WARRANTY</b>	
<b>Standard warranty period</b>	Lifetime

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=130](http://www.tripplite.com/en/products/model.cfm?txtModelID=130).