

SmartRack 42U Value Series Standard-Depth Rack Enclosure Cabinet with Doors, Side, Top and Bottom Panels

MODEL NUMBER: SR2000



Features

- Ships fully assembled
- Ships with flat, locking, front and rear doors, full-length side panels, and roof and bottom panels
- 2000 lb. (907 kg) stationary / 1100 lb. (499 kg) rolling load capacity
- Rear sets of equipment mounting rails adjust in 3/8" increments.
- Toolless accessory mounting slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each slot can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Includes mounting hardware of 40 pieces of M6 cage nuts and 40 pieces of M6 screws
- Textured powder-coat finish for tough resistance to environmental concerns such as deployment in warehouses
- Maximum usable internal depth of 35 in. / 889 mm (front to rear rail)
- Compatibility with airflow optimization accessories, as well as cable management accessories

Highlights

- 4 interior vertical posts with unthreaded square hole openings
- 2000 lb. (907 kg) stationary / 1100 lb. (499 kg) rolling load capacity
- Standard 24" (600 mm) width and 40" (1016 mm) depth for optimizing floor space
- Pre-installed casters and leveling feet roll through standard 7 ft. doorway
- Includes 40 pieces of M6 cage nuts and 40 pieces of M6 screws for equipment mounting

Package Includes

- SmartRack 42U Value Series Standard-Depth Rack Enclosure Cabinet
- (1) Key sets for front / rear doors, and side panels
- (40) M6 Cage Nuts
- (40) M6 Screws
- (40) M6 Nylon Washers
- (2) Stabilizer brackets
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332188212
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Rack Height	42U



Powering Business Worldwide



Rack Depth	Standard
Maximum Device Depth (cm)	88.90
Maximum Device Depth (in.)	35
Maximum Device Depth (mm)	889
Minimum Device Depth (cm)	57.45
Minimum Device Depth (in.)	22.62
Minimum Device Depth (mm)	575
Shipping Dimensions (hwd / in.)	85.00 x 26.00 x 45.50
Shipping Dimensions (hwd / cm)	215.90 x 66.04 x 115.57
Shipping Weight (lbs.)	220.00
Shipping Weight (kg)	99.79
Unit Dimensions (hwd / in.)	76.200 x 23.620 x 39.400
Unit Dimensions (hwd / cm)	197.28 x 59.99 x 100
Unit Weight (lbs.)	169.4
Unit Weight (kg)	76.84
Weight Capacity - Rolling (kg)	499
Weight Capacity - Rolling (lbs.)	1100
Weight Capacity - Stationary (kg)	907
Weight Capacity - Stationary (lbs.)	2000
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.