

13U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST13



Highlights

- 13U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes

Package Includes

- SR2POST13
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

Description

The SR2POST13 2-Post SmartRack Open Frame Rack is an economical way to accommodate 13U of rack space for 19-inch rack-mount applications in limited spaces. Its heavy-duty, aluminum construction can safely support 800 pounds (362.9 kilograms) of rack-mount equipment. The black textured powder-coat finish makes it resistant to scratching while giving it a classic attractive appearance. The SR2POST13 is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions along with bolt-down provisions. Only standard hand tools are required for installation (9/16" wrench and 9/16" socket/ratchet). Multiple units can be bolted together side by side for easy expansion or customization as needed. The SR2POST13 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, and RoHS.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

OVERVIEW	
UPC Code	037332183644
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame



Powering Business Worldwide



PHYSICAL	
Color	Black
Rack Height	13U
Rack Depth	Extra Deep
EIA Mounting Rails	12-24 threaded and numbered vertical mounting rails
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Shipping Dimensions (hwd / in.)	4.53 x 6.50 x 30.71
Shipping Dimensions (hwd / cm)	11.51 x 16.51 x 78.00
Shipping Weight (lbs.)	24.00
Shipping Weight (kg)	10.89
Unit Dimensions (hwd / in.)	28.000 x 20.375 x 13.625
Unit Dimensions (hwd / cm)	71.12 x 51.56 x 12.07
Unit Weight (lbs.)	20
Unit Weight (kg)	9.07
Weight Capacity - Stationary (kg)	363
Weight Capacity - Stationary (lbs.)	800
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.