



42U SmartRack 4-Post Mid-Depth Open Frame Rack - no sides or doors

MODEL NUMBER: SR42UBMDEXPND



Description

The SR42UBMDEXPND offers 36 inches (927 millimeters) of depth opposed to the standard 42 inches. The SR42UBMDEXPND is a 42U SmartRack® enclosure with no doors and no side panels. The 'EXP' version is an expansion model used when several cabinets are bayed together. Its integrated baying tabs make it easy to combine multiple enclosures in rows for data center applications. This enclosure is also compatible with hot-aisle/cold-aisle configurations.

The SR42UBMDEXPND houses 3,000 pounds (1360.8 kilograms) of standard 19-inch rack equipment in 42U. Its front and rear pairs of vertical rails have square mounting holes that are adjustable in quarter-inch increments from four to 28.75 inches. Adjustment is quick and an easy-view depth index ensures consistent rail placement without requiring time-consuming measurements. Each rack space within the enclosure is numbered for ready reference.

Two of the adjustable vertical mounting rails support toolless button-mount 0U installation of up to four compatible PDUs and cable managers. This feature makes it easier to route cabling to rack equipment and reduces cord clutter.

All components of the SR42UBMDEXPND are grounded to the enclosure frame. Front and rear threaded grounding points are provided for connection to the facility earth ground.

To simplify deployment, the SR42UBMDEXPND comes with preinstalled casters that enable it to be easily maneuvered into the desired location, where it can be secured by adjusting the preinstalled levelers. Note: The casters are intended for minor position adjustments and are not designed for moving the enclosure over long distances.

Features

- Ships fully assembled for rapid deployment and roll into place on pre-installed casters, allowing the enclosures to be pre-configured and rolled to the final installation location. Casters are removable.
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring timeconsuming measurements.
- Tool-less accessory mounting rails (2 rails per enclosure) include slots for quick installation of
 compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard
 pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or
 cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Maximum usable internal depth of 31 inches
- Weight ratings of 3000 lbs (1360.8 kgs) stationary and 2250 lbs (1020.6 kgs) rolling.

Highlights

- 42U SmartRack Premium open frame rack
- 36" (927mm) depth (with mounting depth increments from 4 to 28.75") and standard 24" (600mm) width
- 4 interior vertical posts with unthreaded square hole openings
- · Ships fully assembled
- 3000 lbs (1360.8 kgs) stationary / 2250 lbs (1020.6 kgs) rolling load capacity
- Preinstalled casters and leveling feet
- Rolls through standard 7-ft. (2.13 m) doorways
- Includes 50 pieces of M6 cage nuts and 50 pieces of M6 screws (equipment mounting hardware)





- Built in baying tabs allow premium open frame racks to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.
- Leveling feet extend to allow premium open frame racks to be positioned on uneven floors. Levelers are removable.
- Compact design allows the premium open frame racks to roll through standard height commercial doorways.
- Convenient grounding system. All components are grounded to the premium open frame rack structure which includes multiple connections for facility ground.
- Open bottom for cable access.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the premium open frame rack on the inside or outside of the rack.
- Compatibility with all cable management accessories.

Specifications

OVERVIEW	
UPC Code	037332175670
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	42U
Rack Depth	Mid
Maximum Device Depth (cm)	78.74
Maximum Device Depth (in.)	31
Maximum Device Depth (mm)	787
Minimum Device Depth (cm)	10.16
Minimum Device Depth (in.)	4
Minimum Device Depth (mm)	102
Shipping Dimensions (hwd / in.)	85.00 x 26.00 x 37.80
Shipping Dimensions (hwd / cm)	215.90 x 66.04 x 96.01
Shipping Weight (lbs.)	153.00
Shipping Weight (kg)	69.40
Unit Dimensions (hwd / in.)	78.500 x 23.630 x 32.350
Unit Dimensions (hwd / cm)	199.39 x 60.02 x 82.00
Unit Weight (lbs.)	103
Unit Weight (kg)	46.72
Weight Capacity - Rolling (kg)	1,021
Weight Capacity - Rolling (lbs.)	2250





Weight Capacity - Stationary (kg)	1,361	
Weight Capacity - Stationary (lbs.)	3000	
Number of Vertical Mounting Rails	4	
FEATURES & SPECIFICATIONS		
Grounding Details	Front and Back door frames	
Built-in Cable Management	No	
Extra Wide	No	
Pre-Installed Casters	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	UL 60950-1	
Product Compliance	RoHS; CE (Europe); UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.