

25U SmartRack 4-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST25



Highlights

- 25U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST25
- Installation hardware
- 32x pieces of M6 cage nuts, screws, and washers for equipment mounting
- 18x Cable management hooks
- Owner's manual with warranty information

Description

The 25U 4-Post Open Frame Rack helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST25 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 25U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1,000 pounds (453.6 kilograms). The SR4POST25 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST25 provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POST25 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000 lbs (453.6 kgs) of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

| OVERVIEW | |
|----------------------|--|
| UPC Code | 037332157942 |
| Device Compatibility | Patch Panel; Network Switch; UPS; Server |



Powering Business Worldwide



| | |
|--------------------------------------|--|
| Rack Type | Open-Frame |
| PHYSICAL | |
| Color | Black |
| Rack Height | 25U |
| Rack Depth | Standard |
| Maximum Device Depth (cm) | 91.44 |
| Maximum Device Depth (in.) | 36 |
| Maximum Device Depth (mm) | 914 |
| Minimum Device Depth (cm) | 55.88 |
| Minimum Device Depth (in.) | 22 |
| Minimum Device Depth (mm) | 559 |
| Shipping Dimensions (hwd / in.) | 6.50 x 4.53 x 53.70 |
| Shipping Dimensions (hwd / cm) | 16.51 x 11.51 x 136.40 |
| Shipping Weight (lbs.) | 49.00 |
| Shipping Weight (kg) | 22.23 |
| Unit Dimensions (hwd / in.) | 49.300 x 20.200 x 39.300 |
| Unit Dimensions (hwd / cm) | 125.2 x 51.3 x 55.9-91.44 (depth adjustable) |
| Unit Weight (lbs.) | 45 |
| Unit Weight (kg) | 20.41 |
| Weight Capacity - Stationary (kg) | 454 |
| Weight Capacity - Stationary (lbs.) | 1000 |
| Number of Vertical Mounting Rails | 4 |
| Assembly Required | Yes |
| FEATURES & SPECIFICATIONS | |
| Grounding Details | Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames |
| Built-in Cable Management | No |
| Extra Wide | No |
| Pre-Installed Casters | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.