

## 48U Heavy-Duty 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR4POST48HD**



### Highlights

- 48U Heavy-Duty 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

### Package Includes

- SR4POST48HD Heavy-Duty 4-Post Open Frame Rack
- Installation hardware
- (2x) PDU/Cable management brackets
- Owner's manual with warranty information

### Description

This 48U Heavy-Duty 4-Post Open Frame Rack helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST48HD is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 48U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 3,000 pounds (1360.8 kilograms). The SR4POST48HD comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST48HD provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POST48HD supports equipment depths up to 35 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

The optional SRCASTERHDKIT Heavy-Duty Rolling Caster Kit (sold separately) adds mobility to the SR4POST48HD. The SR4POST48HD also supports optional side panels with the SR48SIDE4PHD, a set of two half-size side panels that add a finished look to end-of-row racks in your data center.

### Features

- Weight capacity of 3000 lbs. stationary
- Supports equipment depths up to 35 inches
- Textured, black powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self-squaring design
- Easy assembly
- Optional SRCASTERHDKIT heavy-duty caster kit permits mobile use of 3000 lbs (1360.8 kgs) rolling loads
- Optional SR48SIDE4PHD side panels for end-of-the-row aesthetics

## Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332185778
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	48U
Rack Depth	Standard
Maximum Device Depth (cm)	89.54
Maximum Device Depth (in.)	35.25
Maximum Device Depth (mm)	895
Shipping Dimensions (hwd / in.)	7.00 x 11.00 x 94.00
Shipping Dimensions (hwd / cm)	17.78 x 27.94 x 238.76
Shipping Weight (lbs.)	124.00
Shipping Weight (kg)	56.25
Unit Dimensions (hwd / in.)	90.000 x 24.000 x 35.250
Unit Dimensions (hwd / cm)	228.6 x 60.96 x 89.54
Unit Weight (lbs.)	110
Unit Weight (kg)	49.90
Weight Capacity - Stationary (kg)	1,361
Weight Capacity - Stationary (lbs.)	3000
Number of Vertical Mounting Rails	4
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.