

TAA-Compliant 45U SmartRack 4-Post Open Frame Rack

MODEL NUMBER: **SR4POSTAA**



Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 45U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Description

Tripp Lite's TAA-Compliant 45U 4-Post Open Frame Rack helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POSTAA is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 45U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1000 lb. The SR4POSTAA comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side. The SR4POSTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

The open design of the SR4POSTAA provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POSTAA supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332154057
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	45U
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Shipping Dimensions (hwd / in.)	4.53 x 6.50 x 87.99
Shipping Dimensions (hwd / cm)	11.51 x 16.51 x 223.49
Shipping Weight (lbs.)	58.40
Shipping Weight (kg)	26.49
Unit Dimensions (hwd / in.)	84.020 x 20.200 x 34.300
Unit Dimensions (hwd / cm)	214.122 x 51.44 x 55.88-91.44
Unit Weight (lbs.)	73
Unit Weight (kg)	33.11
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.