



# SmartRack Roof-Mounted Fan Panel - 6-120V high-performance fans; 630 CFM, 5-15P plug

MODEL NUMBER: SRFANROOF



### **Highlights**

- Roof Mount Fan Panel 120V
- Ideal for increasing the ventilation of SmartRacks
- Features (6) 120V fans mounted in a roof panel, 6-ft. (1.83 m)
- Toolless mounting hardware included
- · Cold rolled steel with black finish
- 2A current draw

## **Package Includes**

 Fan panel with 6-ft. (1.83 m) power cord, mounting hardware

#### **Description**

SmartRack® SRFANROOF is ideal for increasing the ventilation in all rack enclosure server cabinets. The unit features six 120V high-performance fans mounted in a roof panel, six-foot (1.8-meter) cord with NEMA 5-15P input plug, and includes toolless mounting hardware.

COMPATIBLE SMARTRACK ENCLOSURES: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR45UB, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA and other SmartRack enclosures that specify the use of this accessory.

#### **Features**

- Ideal for increasing the ventilation in all rack enclosure server cabinets
- Unit features (6) 120V high performance fans mounted in a roof panel
- 6-ft. (1.83 m) cord with NEMA 5-15P input plug
- Includes toolless mounting hardware
- Compatible SmartRack Enclosures: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR45UB, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other SmartRack enclosures that specify the use of this accessory

# **Specifications**

OVERVIEW		
UPC Code	037332144546	
Accessory Type	Cooling Accessories; Fan Panel	
Accessory Class	Cooling Accessories	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	





Nominal Input Voltage Description	120V AC 50/60 Hz	
Input Connection Type	NEMA 5-15P	
Input Plug Features	NEMA 5-15P	
Voltage Compatibility (VAC)	120	
Input Frequency	50/60 Hz	
Input Cord Length (ft.)	6	
Input Cord Length (m)	1.83	
COOLING		
Cooling Type	Passive	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Lighted ON/OFF rocker switch	
PHYSICAL		
Shipping Dimensions (hwd / in.)	15.00 x 23.25 x 37.00	
Shipping Dimensions (hwd / cm)	38.10 x 59.06 x 93.98	
Shipping Weight (lbs.)	34.00	
Shipping Weight (kg)	15.42	
Unit Dimensions (hwd / in.)	3.000 x 23.500 x 35.500	
Unit Dimensions (hwd / cm)	5.33 x 55.63 x 90.17	
Unit Weight (lbs.)	22	
Unit Weight (kg)	9.98	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.