



SmartRack Heavy-Duty Sliding Shelf (200 lbs / 90.7 kgs capacity; 28.3 in/719 mm Deep)

MODEL NUMBER: SRSHELF4PSLHD







Highlights

- Heavy Duty Sliding Shelf supports up to 200 lbs (90.7 kgs)
- Designed for 4 post rack mounting
- 28.3 inch / 72 cm shelf depth
- Extendible shelf accommodates tower units, monitors, and other equipment
- Cold rolled steel with black finish
- Required mounting hardware included

Package Includes

• Shelf and mounting hardware

Description

SmartRack® SRSHELF4PSLHD is a heavy-duty sliding shelf for installation in rack cabinets. The SRSHELF4PSLHD has a 28.3-inch (720-millimeter) depth (29.5 inches including handle) and can support up to 200 pounds (90.7 kilograms). This extendable shelf can accommodate tower units, monitors and other equipment. It is designed for 4-post rack mounting and the required mounting hardware is included. Expandable mounting rails supports installation in racks with front to rear rail distances between 28 inches (710 millimeters) minimum and 46 inches (1170 millimeters) maximum.

Features

- · Heavy duty sliding shelf for installation in rack cabinets
- 28.3 in. / 72.4cm depth (29.5 in. / 74.9cm including handle)
- Supports up to 200 lbs (90.7 kgs)
- This extendable shelf can accommodate tower units, monitors and other equipment
- Designed for 4 post rack mounting and the required mounting hardware is included
- Expandable mounting rails supports installation in racks with front to rear rail distances between 28 in. / 71cm minimum and 46 in. / 117cm maximum

Specifications

OVERVIEW		
UPC Code	037332140654	
Accessory Type	Rack Shelves	
Accessory Class	Rack Accessories	
PUVOIOAI		
PHYSICAL		
Shipping Dimensions (hwd / in.)	3.00 x 20.20 x 31.00	
Shipping Dimensions (hwd / cm)	7.62 x 51.31 x 78.74	





Shipping Weight (lbs.)	23.60	
Shipping Weight (kg)	10.70	
Unit Dimensions (hwd / in.)	2.360 x 19.000 x 30.000	
Unit Dimensions (hwd / cm)	5.99 x 48.21 x 76.48	
Unit Weight (lbs.)	24	
Unit Weight (kg)	10.89	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.