



SmartRack 5U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: SRWF5U



Wall-mount cabinet secures and organizes 5U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 20 inches deep, but extends less than 10 inches from wall.

Description

The SRWF5U SmartRack 5U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends less than 10 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels. In addition to 5U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF5U comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable WorkspacePerfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the wayHouses EIA-standard 19 in. rack equipment in 5U of spaceLow-profile vertical-mount cabinet extends less than 10 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panelsAlso includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deepMaximum load capacity of 150 lbs (68 kgs)

Keeps Important Equipment SecureTop panel and reversible front door lock securely to help prevent damage, tampering or theftVented cabinet keeps equipment coolConvenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment InstallationShips fully assembled for quick installationWall-mounting holes spaced 16 in. apart for standard wall stud placementRails adjust easily—unscrew them, slide them to desired depth, and screw them back inThreaded mounting holes support M6 or 12-24 mountingRack spaces marked for easy reference

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 5U of 19 in. rack equipment up to 20 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF5U SmartRack 5U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



Meets Payment Card Industry StandardsProvides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332163981
Device Compatibility	Patch Panel; Network Switch
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	50
Rack Depth	Shallow
Maximum Device Depth (cm)	50.80
Maximum Device Depth (in.)	20
Maximum Device Depth (mm)	508
Shipping Dimensions (hwd / in.)	29.00 x 12.90 x 31.70
Shipping Dimensions (hwd / cm)	73.66 x 32.77 x 80.52
Shipping Weight (lbs.)	57.00
Shipping Weight (kg)	25.85
Unit Dimensions (hwd / in.)	28.800 x 25.600 x 9.700
Unit Dimensions (hwd / cm)	80.52 x 73.66 x 32.77
Unit Weight (Ibs.)	45
Unit Weight (kg)	20.41
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	





Product Warranty Period (Worldwide)

5-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.