

SmartRack 12U Flat-Pack Low-Profile Switch-Depth Wall-Mount Pivoting 2-Post Open Frame Rack

MODEL NUMBER: **SRWO12US**



Open frame rack stores 12U of 19-inch rack equipment up to 18 inches deep in locations with limited floor space where a locked enclosure is not required.. Pivots to allow easy rear access to equipment and cabling.

Description

The SRWO12US SmartRack 12U Flat-Pack Low-Profile Switch-Depth Wall-Mount Pivoting 2-Post Open Frame Rack stores and organizes EIA-standard 19-inch rack equipment compatible with 2-post mounting in network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required. Constructed from heavy-duty steel with a durable black powder-coated finish, the rack has a maximum load capacity of 150 lbs (68 kgs).

The open frame design pivots to allow unrestricted access for installing, configuring and servicing equipment and cabling from any direction. The rack is simple to assemble and mount to the wall.

Threaded 12-24 mounting holes and numbered rack spaces make equipment installation easy. Included locking pins secure the frame in position while pivoted for mounting equipment. The vertical mounting rails accommodate equipment up to 18 inches deep, such as network switches and patch panels. Assembly and equipment-mounting hardware is included.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required
- Maximum load capacity of 150 lbs (68 kgs)

2-Post Open-Frame Design

- Pivoting frame allows easy access for installing, configuring and servicing equipment and cabling from any direction
- Stores and organizes EIA-standard 19 in. rack equipment compatible with 2-post mounting in 12U of space

Easy Assembly and Installation

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails accommodate equipment up to 18 in. deep, such as network switches and patch panels

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Pivots to allow easy rear access to equipment and cabling
- Stores 12U of 19 in. rack equipment up to 18 in. deep
- Simple to assemble and mount
- Assembly and equipment-mounting hardware included

Package Includes

- Mounting template
- (2) Wall-mount A frames
- Equipment mounting frame
- (2) Pivot bearings
- (2) T bolts
- (4) Washers
- (2) M10 lock nuts
- (2) Locking pins
- (24) 12-24 equipment mounting screws
- Owner's manual



Powering Business Worldwide



- Locking pins prevent the frame from moving during equipment installation
- Rails support threaded-hole equipment mounting
- Rack spaces numbered for easy reference
- Includes assembly and equipment-mounting hardware

Specifications

OVERVIEW	
UPC Code	037332156761
Device Compatibility	Patch Panel; Network Switch
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Shallow
Maximum Device Depth (cm)	45.72
Maximum Device Depth (in.)	18
Maximum Device Depth (mm)	457
Shipping Dimensions (hwd / in.)	4.10 x 24.40 x 20.10
Shipping Dimensions (hwd / cm)	10.41 x 61.98 x 51.05
Shipping Weight (lbs.)	16.00
Shipping Weight (kg)	7.26
Unit Dimensions (hwd / in.)	31.040 x 19.760 x 20.350
Unit Dimensions (hwd / cm)	78.04 x 50.19 x 51.69
Unit Weight (lbs.)	15
Unit Weight (kg)	6.80
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.