


12-Outlet Power Strip with Surge Protection, 15 ft. (4.57 m) Cord, 1050 Joules, 36 in. length

MODEL NUMBER: **SS3612**



Highlights

- 12 outlets
- 15-ft. (4.57 m) cord
- 36-in. length
- 1050-joule rating

Package Includes

- SS3612 Power Strip/Surge Suppressor
- Set of adjustable mounting clips
- Warranty information
- Instruction manual

Description

The SS3612 power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more. Includes 12 NEMA 5-15R outlets with 2.48-in. center-to-center spacing, 15-ft. (4.57 m) AC line cord and adjustable mounting clips for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 1050 joules. This corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive gray housing with black output receptacles.

PLUG/OUTLETS: Input: NEMA 5-15P Output: 12 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: 3-ft. corded vertical/raceway power distribution strip

SURGE SUPPRESSION: 1050 joules

Features

- 3-ft. power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more
- Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 1050 joules
- 12 NEMA 5-15R outlets with 2.48-in. center-to-center spacing
- 15-ft. (4.57 m) AC line cord
- Adjustable mounting clips for installation in a wide variety of applications
- Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket
- Rugged all-metal housing
- Lighted power switch with transparent guard to prevent accidental shutoff
- 15A resettable circuit breaker
- Attractive gray housing with black output receptacles

Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332186409
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	22000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Outlet Spacing	2.48-in. center-to-center spacing
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker and lighted 2-position power switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
UL1449 Let Through Rating	500V UL verified
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	



Powering Business Worldwide



Power Cord Color	Black
Housing Color	Silver
Included Mounting Accessories	Set of adjustable mounting clamps
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	2.48
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 4.60 x 39.80
Shipping Dimensions (hwd / cm)	6.35 x 11.68 x 101.09
Shipping Weight (lbs.)	3.90
Shipping Weight (kg)	1.77
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 36.000
Unit Dimensions (hwd / cm)	3.18 x 4.11 x 91.44
Unit Weight (lbs.)	3.19
Unit Weight (kg)	1.45
Outlet Spacing	2.48-in. center-to-center spacing
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.