



8-Outlet Power Strip with Surge Protection, 6 ft. (1.83 m) Cord, 1650 Joules, 48 in. length

MODEL NUMBER: SS480806



Easily add extra surge-protected power outlets with extra wide spacing in computer rooms, workbenches, repair shops, labs or anywhere that needs to connect many electrical devices simultaneously to a single AC wall outlet.

Features

Multi-Outlet 120V Power Distribution and Surge Protection for Locations with Limited Free Space

- 1800W, 120V, 15A, corded, multi-outlet power strip that connects multiple electrical devices in close proximity to a single AC wall socket
- Contains an integral surge protector to eliminate the need for a separate desktop unit that can clutter up your work space
- · Saves the time and cost of installing new outlets in un-powered areas
- Ideal for branch circuit power distribution to telecommunications, computers or internetworking equipment in rack enclosures, workbenches, table tops, work stations, offices, factories, repair shops, test stands and engineering labs

8 Widely Spaced Outlets That Fit Transformers or AC Adapters without Blocking Adjacent Outlets

- Features 8 NEMA 5-15R outlets that are compatible with all standard electrical equipment
- Each outlet is spaced 5.28 inches apart (center to center) wide enough to fit transformers or AC adapters without blocking adjacent outlets, so you can fully utilize the power strip all the time

Premium-Grade, Surge Suppression to Protect Against Destructive Surges and Line Noise

 Contains a premium-grade surge suppressor rated at 1650 Joules that goes well beyond competing surge protectors, giving you an exceptional level of AC transient surge and EMI/RFI line noise protection for computers and other sensitive electronics

Adjustable Vertical and Horizontal Mounting Options

- A convenient method of optional horizontal or vertical power distribution
- Its 48-in. length and strip-style form factor fits in the most confined spaces unobtrusively
- Easy-to-install with adjustable mounting clamps

Premium Safety Features

Highlights

- 8 NEMA 5-15R outlets with 5.28-in. center-to-center spacing – wide enough for transformers without blocking adjacent outlets
- Rated at 1800W, 120V, 15A, featuring a resettable circuit breaker to prevent circuit overloads
- Integral, premium-grade, 1650-Joule surge suppressor to protect sensitive electronics from destructive AC transient surges
- Vertical or horizontal mounting with adjustable mounting clamps
- Rocker-style, illuminated power switch with locking safety cover to prevent accidental turn offs
- Certified to meet UL 1449 3rd Edition and UL 1363 standards

Package Includes

- SS480806 Power Strip/Surge Suppressor
- · Set of adjustable mounting clips
- Warranty information
- · Instruction manual



- Features an illuminated, rocker-style power switch with a locking, transparent guard to prevent accidental turn offs
- An integral, 15-amp resettable circuit breaker prevents dangerous circuit overloads that can irreversibly damage connected equipment

Rugged, Durable Housing

• A rugged, all-metal housing is durably constructed making it a great solution for industrial applications

• An attractive gray housing with stylish black receptacles match the decor of most professional settings

Specifications

OVERVIEW		
UPC Code	037332186430	
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output Receptacles	(8) 5-15R	
Circuit Breaker (amps)	15	
Outlet Spacing	5.28-in. center-to-center spacing	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	No	
Switches	Combination AC circuit breaker and lighted 2-position power switch controls power to all outlets	
Locking Switch Cover	Transparent locking switch cover	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1650	
UL1449 Let Through Rating	500V UL verified	





EMI / RFI Filtering	Yes	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Power Cord Color	Black	
Housing Color	Silver	
Included Mounting Accessories	Set of adjustable mounting clamps	
Mounting Holes or Slots	No	
Outlets Measurement (Center to Center)	5.28	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	2.40 x 3.40 x 51.90	
Shipping Dimensions (hwd / cm)	6.10 x 8.64 x 131.83	
Shipping Weight (lbs.)	3.30	
Shipping Weight (kg)	1.50	
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 48.000	
Unit Dimensions (hwd / cm)	3.18 x 4.11 x 121.9	
Unit Weight (lbs.)	2.64	
Unit Weight (kg)	1.20	
Outlet Spacing	5.28-in. center-to-center spacing	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.